

Photonics.com - February 2012

New MK52 Negative-Stiffness Optical Vibration Isolation Table

Minus K Technology, a leading manufacturer of vibration isolation products has partnered with Kinetic Systems, Inc. in designing a new, versatile, ultra-low natural frequency optical table isolation system

The MK52 negative-stiffness optical table achieves 0.5 Hz or lower vertical and horizontal natural frequencies without limiting its ability to support static loads. When adjusted to a 0.5 Hz natural frequency, the MK52 achieves 93 percent isolation efficiency at 2 Hz, 99 percent at 5 Hz, and 99.7% percent at 10 Hz.



The MK52 Optical Vibration Isolation Table can be configured for a wide variety of locations and applications - wherever external vibrations can adversely affect the operation of sensitive equipment. Ultra-low natural frequencies, high internal structural frequencies, and excellent vertical and horizontal isolation efficiencies make the system well-suited to applications such as analytical balances, cell injection, confocal microscopes, patch clamping, optical microscopes, wafer probing, sensor calibration and laser applications, in fields such as semiconductor processing, telecommunications, aerospace engineering and medical research.